

Technical data sheet T520

Specification Seating element 1,5 seater, left

Dimensions in mm	Backrest:	H:	330
	Seat:	H:	400
Total:		H:	685
		W (ArmR):	1110
		D:	885
Packaging data	Weight:	kg	30,5
	Volume:	m³	0,33



Basic equipment

Benefit

Backrest	Backrest height: 330 mm, completely upholstered.	"Free standing" - individual placing possible. The backrest serves also as armrest.
Upholstery	Seat upholstery, 60 mm pocket springs + 65 mm foam, CFC and CHC-free (pure foam).	Very comfortable.
Frame/metal parts	Aluminium, polished.	High-quality look. Easy to clean below.
Glides	Change glides for hard and soft floors, from felt respectively plastic.	You can turn over the glides to match different flooring (hard/soft). High satiability and alteration options to match the flooring. Ideal stability and protection of the floor.
Materials (fabric)	Several fabric collections in various colours. Additional colours (fabric/leather) on request.	Individual design is possible. Several fabrics and colours are available.
Materials	All materials are segregated and recyclable.	Environmentally friendly.
Certification	Quality management system DIN EN ISO 9001:2008, VO (EG) No. 1221/2009 (EMAS), Environmental management system DIN EN ISO 14001:2009, OHSAS, EcoVadis gold, Commitment to sustainability.	High-quality product.
Standards	Tested for contaminants. GS-symbol for having tested safety.	
Warranty and return	10 years warranty. Complete return and recycling guarantee.	Exchange of parts free of charge within the guaranteed periods.

Disassembly instructions are available upon request for any interstuhl product

Technical data sheet T520

Specification Seating element 1,5 seater, left

Dimensions in mm	Backrest:	H:	330
	Seat:	H:	400
	Total:	H:	685
		W (ArmR):	1110
		D:	885
Packaging data	Weight:	kg	30,5
	Volume:	m³	0,33



Options	Benefit
Materials (fabric)	Permanent flame retardant version upon request.
	Fire resistance.

Accessories	Cushion 40 x 40 cm in various materials (fabric and leather available (seperate model-no. T550). Electrification and link element upon request.

Disassembly instructions are available upon request for any interstuhl product